

LaserForm[®] AlSi10Mg (A)

AlSi10Mg fine-tuned for use with ProX[®] DMP 320 metal printer producing industrial parts with a combination of good mechanical properties and good thermal conductivity.

LaserForm AlSi10Mg (A) is formulated and fine-tuned specifically for 3D Systems DMP 320 metal 3D Printers to deliver high part quality and consistent part properties. The print parameter database that 3D Systems provides together with the material has been extensively developed, tested and optimized in 3D Systems' part production facilities that hold the unique expertise of printing 500,000 challenging metal production parts in various materials year over year. And for your 24/7 production 3D Systems' thorough Supplier Quality Management System guarantees consistent, monitored material quality for reliable results.

Material Description

AlSi10Mg combines silicon and magnesium as alloying elements, which results in a significant increase in strength and hardness compared to other aluminum alloys. Due to the very rapid melting and solidification during Direct Metal Printing, LaserForm AlSi10Mg (A) in as-printed condition shows fine microstructure and high strengths.

In the aerospace and automotive industry, LaserForm AlSi10Mg (A) is used for its light weight. Both innovative approaches to mold design and specific heat exchanger applications make use of the high thermal conductivity of this alloy.

Mechanical Properties^{1,2}

MEASUREMENT	CONDITION	METRIC			U.S.		
		AS-BUILT	AFTER STRESS RELIEF	DIRECT AGEING	AS-BUILT	AFTER STRESS RELIEF	DIRECT AGEING
Young's modulus (GPa ksi)	ASTM E8M	71 ± 2	73 ± 6	73 ± 6	10300 ± 300	10600 ± 900	10600 ± 900
Ultimate strength (MPa ksi)	ASTM E8M						
Horizontal direction - XY Vertical direction - Z		450 ± 30 420 ± 60	310 ± 20 300 ± 20	420 ± 30 410 ± 40	65 ± 4 61 ± 9	45 ± 3 44 ± 3	61 ± 4 60 ± 6
Yield strength Rp0.2% (MPa ksi)	ASTM E8M						
Horizontal direction - XY Vertical direction - Z		260 ± 30 230 ± 40	200 ± 20 170 ± 20	270 ± 20 260 ± 40	38 ± 4 33 ± 6	29 ± 3 25 ± 3	39 ± 3 38 ± 6
Plastic elongation (%)	ASTM E8M						
Horizontal direction - XY Vertical direction - Z		8 ± 4 5 ± 2	12 ± 2 9 ± 4	6 ± 2 3 ± 2	8 ± 4 5 ± 2	12 ± 2 9 ± 4	6 ± 2 3 ± 2
Hardness, Rockwell B (HRB)	ASTM E18	71 ± 4	50 ± 6	72 ± 4	72 ± 4	50 ± 6	72 ± 4
Impact toughness ³ , typical (J ft-lb)	ASTM E23	3-4	5-12	1-3	2-3	4-9	1-2

Thermal Properties⁴


MEASUREMENT	CONDITION	METRIC	U.S.
Thermal conductivity (W/(m.K) Btu/(h.ft ² .°F))	at 25 °C / 77 °F	113	65
CTE - Coefficient of thermal expansion (µm/(m.°C) µ inch/(inch . °F))	in the range of 20 to 100 °C	20.9	11.6
Melting range (°C °F)		557 - 596	543 - 613

¹ Parts manufactured with standard parameters on a ProX DMP 320, Config B

² Values based on average and double standard deviation

³ Tested with Charpy V-notch impact test specimens type A at room temperature


⁴ Values based on literature



LaserForm[®] AlSi10Mg (A)

Physical Properties


MEASUREMENT	METRIC	U.S.
Density		
Relative, based on pixel count ¹ (%)	>99.9	>99.9
Absolute theoretical ² (g/cm ³ lb/in ³)	2.68	0.097



Microstructure as built

Surface Quality³

MEASUREMENT	SAND BLASTED METRIC	SAND BLASTED U.S.
Surface Roughness R _a		
Vertical direction (Z) (µm µin)	7 - 10	275 - 390




Microstructure after stress release

Chemical Composition

The chemical composition of LaserForm AlSi10Mg (A) conforms to the requirements EN AC 43100, and is indicated in the table below in wt%.

ELEMENT	% OF WEIGHT
Al	Balance
Si	9.00-11.00
Mg	0.20-0.45
Fe	≤0.55
Cu	≤0.10
Mn	≤0.35
Ni	≤0.05
Zn	≤0.10
Pb	≤0.05
Sn	≤0.05
Ti	≤0.15



Microstructure after direct ageing



www.3dsystems.com

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

©2018 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems, ProX and LaserForm are registered trademarks and the 3D Systems logo is a trademark of 3D Systems, Inc.

¹ Parts manufactured with standard parameters on a ProX DMP 320, Config B

² Values based on literature